

Eaton C0005P8DSES

Catalog Number: C0005P8DSES

Eaton, type AP, industrial control transformer, pv: 440v, taps: 2 at +2.5% fcan, 2 at -2.5% fcbn, sv: 110/220v, 115°C, 5000 va, cu magnet wire, elec. shield, frame: 256



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Type AP industrial control transformer	C0005P8DSES
	UPC
	782114889442
Product Length/Depth	Product Height
8.701 in	12 in
Product Width	Product Weight
11 in	106 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Certifications
	UL Recognized
	Catalog Notes
	Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

Physical Attributes

Coil material

Copper windings

Design

AP

Frame

256

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Wiring connection

405E

Performance Ratings

Primary voltage

440 V

Temperature rating

115°C

Volt ampere rating

5000 VA

Secondary voltage

110/220 V

Miscellaneous

Modification 1

Side/wall mounted

Special features

Electrostatically Shielded

Resources

Brochures

Industrial control transformers brochure

dry-type distribution transformer-flex center line card

Catalogs

Transformer distribution catalog, volume 2, tab 2

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Transformer consulting application guide

Eaton Specification Sheet - C0005P8DSES



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)