

# Eaton C0005P8TSES

Catalog Number: C0005P8TSES

Eaton, type AP, industrial control transformer, control transformer, AP, 600v, 2@+2.5%, 2@-2.5%, 12/0240v, 115, 5 kva, electrostatic shield, frame 256, wiring diagram 405d, side/wall mount, 60 hz, open



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type AP industrial control transformer	C0005P8TSES
	<b>UPC</b>
	786680018473
<b>Product Length/Depth</b>	<b>Product Height</b>
8.701 in	12 in
<b>Product Width</b>	<b>Product Weight</b>
11 in	85 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	UL Recognized
	<b>Catalog Notes</b>
	60 Hz

## Physical Attributes

### Enclosure

Open

### Frame

256

### Mounting method

Side wall

### Tap size

2@+2.5%, 2@-2.5%

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

600 V

### Temperature rating

115°C

### Volt ampere rating

5

### Secondary voltage

12/240 V

## Resources

### Brochures

[dry-type distribution transformer-flex center line card](#)

[Industrial control transformers brochure](#)

### Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0005P8TSES](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)