

Eaton C0007P7GB

Catalog Number: C0007P7GB

Eaton Type AP industrial control transformer, Copper windings, None, 115°C, Industrial control transformer, 7000 VA, 416A, Bottom mounted, AP, 100, 240 x 480 V, 120/240 V



Photo is representative

General specifications

Product Name

Eaton Type AP industrial control transformer

Catalog Number

C0007P7GB

UPC

786680182020

Product Length/Depth

10.197 in

Product Height

10.748 in

Product Width

10.748 in

Product Weight

119 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Recognized from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board



Powering Business Worldwide

Physical Attributes

Coil material

Copper windings

Design

AP

Frame

100

Tap size

None

Wiring connection

416A

Performance Ratings

Primary voltage

240 x 480 V

Temperature rating

115°C

Volt ampere rating

7000 VA

Secondary voltage

120/240 V

Miscellaneous

Modification 1

Bottom mounted

Resources

Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0007P7GB](#)