

Eaton C0007P8TSES

Catalog Number: C0007P8TSES

Eaton, type AP, industrial control transformer, control transformer, AP, 600v, 2@+2.5%, 2@-2.5%, 120/240v, 115, 7.5 kva, electrostatic shield, frame 257, wiring diagram 405d, side/wall mount, 60 hz, open



Photo is representative

General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Type AP industrial control transformer | C0007P8TSES |
| | UPC |
| | 786680018497 |
| Product Length/Depth | Product Height |
| 11 in | 12 in |
| Product Width | Product Weight |
| 11 in | 118 lb |
| Warranty | Compliances |
| Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Certifications |
| | UL Recognized |
| | Catalog Notes |
| | 60 Hz |

Physical Attributes

Enclosure

Open

Frame

257

Mounting method

Side wall

Tap size

2@+2.5%, 2@-2.5%

Performance Ratings

Frequency rating

60 Hz

Primary voltage

600 V

Temperature rating

115°C

Volt ampere rating

7.5

Secondary voltage

120/240 V

Resources

Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0007P8TSES](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)