

Eaton C0007P8XSES

Catalog Number: C0007P8XSES

Eaton, type AP, industrial control transformer, pv: 380v, taps: 2 at +2.5% fcan, 2 at -2.5% fcbn, sv: 120/240v, 115°C, 7000 va, cu magnet wire, elec. shield, frame: 258



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Type AP industrial control transformer	C0007P8XSES
	UPC
	786680018503
Product Length/Depth	Product Height
11.38 in	12 in
Product Width	Product Weight
10.75 in	147 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Certifications
	UL Recognized
	Catalog Notes
	Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

Physical Attributes

Coil material

Copper windings

Design

AP

Frame

258

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Wiring connection

405F

Performance Ratings

Primary voltage

380 V

Temperature rating

115°C

Volt ampere rating

7000 VA

Secondary voltage

120/240 V

Miscellaneous

Modification 1

Side/wall mounted

Special features

Electrostatically Shielded

Resources

Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0007P8XSES](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)