

Eaton C0010P7LS

Catalog Number: C0010P7LS

Eaton, type AP, industrial control transformer, pv: 240 x 480v, taps: none, sv: 277v, 115°c, 10000 va, cu magnet wire, frame: 258



Photo is representative

General specifications

Product Name
Eaton Type AP industrial control transformer

Catalog Number
C0010P7LS

UPC
786680071225

Product Length/Depth
10.748 in

Product Height
12 in

Product Width
11.378 in

Product Weight
140 lb

Warranty

Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications
UL Recognized

Catalog Notes

Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

Physical Attributes

Coil material

Copper windings

Design

AP

Frame

258

Tap size

None

Wiring connection

531E

Performance Ratings

Primary voltage

240 x 480 V

Temperature rating

115°C

Volt ampere rating

10000 VA

Secondary voltage

277 V

Miscellaneous

Modification 1

Side/wall mounted

Resources

Brochures

[dry-type distribution transformer-flex center line card](#)

[Industrial control transformers brochure](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

[Transformer distribution catalog, volume 2, tab 2](#)

Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0010P7LS](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)