

# Eaton C0015P7GB

Catalog Number: C0015P7GB

Eaton, type AP, industrial control transformer, pv: 240 x 480v, taps: none, sv: 120/240v, 115°C, 15000 va, cu magnet wire, frame: 134



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type AP industrial control transformer	C0015P7GB

<b>UPC</b>
786680184963

<b>Product Length/Depth</b>
10.433 in

<b>Product Height</b>
12.008 in

<b>Product Width</b>
13.189 in

<b>Product Weight</b>
163 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Recognized from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

### Catalog Notes

Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

## Physical Attributes

### Coil material

Copper windings

### Design

AP

### Frame

134

### Tap size

None

### Wiring connection

416A

## Performance Ratings

### Primary voltage

240 x 480 V

### Temperature rating

115°C

### Volt ampere rating

15000 VA

### Secondary voltage

120/240 V

## Miscellaneous

### Modification 1

Bottom mounted

## Resources

### Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

### Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0015P7GB](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)