

# Eaton C0015P8XSES

Catalog Number: C0015P8XSES

Eaton, type AP, industrial control transformer, pv: 380v, taps: 2 at +2.5% fcan, 2 at -2.5% fcbn, sv: 120/240v, 115°C, 15000 va, cu magnet wire, elec. shield, frame: 259



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type AP industrial control transformer	C0015P8XSES
	UPC
	786680018541
<b>Product Length/Depth</b>	<b>Product Height</b>
13.16 in	14 in
<b>Product Width</b>	<b>Product Weight</b>
10.42 in	190 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	<b>Certifications</b>
	UL Recognized
	<b>Catalog Notes</b>
	Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

## Physical Attributes

### Coil material

Copper windings

### Design

AP

### Frame

259

### Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

### Wiring connection

405F

## Performance Ratings

### Primary voltage

380 V

### Temperature rating

115°C

### Volt ampere rating

15000 VA

### Secondary voltage

120/240 V

## Miscellaneous

### Modification 1

Side/wall mounted

### Special features

Electrostatically Shielded

## Resources

### Brochures

[dry-type distribution transformer-flex center line card](#)

[Industrial control transformers brochure](#)

### Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - C0015P8XSES](#)

[Transformer consulting application guide](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)