

Eaton C0350E2V

Catalog Number: C0350E2V

Eaton, type MTE, industrial control transformer, pv:
208/230/400/460/575v, taps: none, sv: 24/115/230v, 55°C, 350 va ,
cu magnet wire



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0350E2V
	UPC
	782116910267
Product Length/Depth	Product Height
8.5 in	6 in
Product Width	Product Weight
6 in	25 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	cUL Certified
	UL Listed
	CSA Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material
Copper windings

Design
MTE

Tap size
None

Performance Ratings

Primary voltage
208/230/400/460/575 V

Temperature rating
55°C

Volt ampere rating
350 VA

Secondary voltage
24/115/230 V

Resources

Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

[Transformer distribution catalog, volume 2, tab 2](#)

Specifications and datasheets

[Eaton Specification Sheet - C0350E2V](#)

[Transformer consulting application guide](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)