

Eaton C25DNJ250B-GL

Catalog Number: C25DNJ250B-GL

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (vertical in-line), 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, 2 and 3 pole, Contactor, Two-pole, Global listed, D1, Box lugs (posidrive setscrew)

General specifications



Photo is representative

Product Name

Eaton definite purpose contactor

UPC

786685699882

Product Height

3.75 in

Product Weight

1.3 lb

Catalog Number

C25DNJ250B-GL

Product Length/Depth

3.35 in

Product Width

2.4 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

RoHS Compliant
CE Marked

Certifications

UL Listed file E1491 (Guide Number NLDX2)
CSA Certified

defaultTaxonomyAttributeLabel

Accessories

Mounting plate

Number Of Poles

Two-pole

Options

Global listed

Type

Non-reversing

Auxiliary contacts

Quick connect (vertical in-line)

Coil voltage

208-240 Vac, 50-60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Model

Contactors

Series

D1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C25DNJ2 AutoCAD 2D Footprint

C25DNJ2 3D Inventor

C25DNJ2 2D PDF

C25DNJ2 2D Drawing Xchange

C25DNJ2 AutoCAD 2D Footprint (mm)

C25DNJ2 3D Model Xchange

Specifications and datasheets

Eaton Specification Sheet - C25DNJ250B-GL