

Eaton C30CNM20T02T0

Catalog Number: C30CNM20T02T0

Eaton C30CN mechanically held lighting contactor, 30 A, 1 NO, 2 NO, 30 A, Two-pole, Mechanically and electrically held, C30 Series, Open, 24 V at 60 Hz, 20V at 50 Hz

General specifications



Photo is representative

Product Name	Catalog Number
Eaton C30CN mechanically held lighting contactor	C30CNM20T02T0
	UPC
	786685015385
Product Length/Depth	Product Height
7.39 in	3.86 in
Product Width	Product Weight
4.18 in	3 lb
Warranty	Certifications
1 year	UL Listed

defaultTaxonomyAttributeLabel

Resources

Series

C30CN

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Quick Selector - Lighting Contactors](#)

[Eaton Specification Sheet - C30CNM20T02T0](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)