

Eaton C361SD162

Catalog Number: C361SD162

Type C361 Flange Mounted Disconnect Switch, Switch and operating mechanism with handle, 4 in handle, #2-14 AWG Cu/Al, NEMA 1 or 12 enclosure, Right-hand mounting, 15 hp at 208 Vac fuse clip rating, 60A, 7-16 in depth

General specifications




Photo is representative

Product Name

Eaton rotary disconnect main switch

Catalog Number

C361SD162

UPC

782113599243

Product Length/Depth

18.7 in

Product Height

9.5 in

Product Width

11.5 in

Product Weight

14 lb

Warranty

1 year

Certifications

CSA Certified

UL Listed

Catalog Notes

Maximum horsepower ratings refer to switch only. Fuse clips are non-interchangeable type for Class H, J, K, or R type fuses only. Components individually boxed and shipped in overpack carton.

Physical Attributes

Enclosure

NEMA 1, NEMA 12

Handle Length

4 in

Mounting

Right

Type

Switch and operating mechanism with handle

Wire size

#14-2 AWG Cu/Al

Performance Ratings

Amperage Rating

60A

Depth range

7-16 in

Fuse clip rating

60 A at 600 V

HP rating - max

15 hp at 208 Vac, 15 hp at 240 Vac, 30 hp at 480 Vac, 50 hp at 600 Vac, 10 hp at 250 Vdc

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - C361SD162](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)