

Eaton C361SE1263

Catalog Number: C361SE1263

Type C361 Flange Mounted DS, Switch and operating mechanism with handle, 4 in handle, #1/0-14 AWG Cu/Al, NEMA 1 or 12 enclosure, Right-hand MTG, 25 hp at 208 Vac, 30 hp at 240 Vac, 100A at 250/600V fuse clip rating, 100A, 7-16 in depth

General specifications



Photo is representative

Product Name

Eaton rotary disconnect main switch

UPC

782113599281

Product Height

9.8 in

Product Weight

16.05 lb

Certifications

CSA Certified

UL Listed

Catalog Number

C361SE1263

Product Length/Depth

19.7 in

Product Width

13.1 in

Warranty

1 year

Catalog Notes

Maximum horsepower ratings refer to switch only. Fuse clips are non-interchangeable type for Class H, J, K, or R type fuses only. Components individually boxed and shipped in overpack carton.

Physical Attributes

Enclosure

NEMA 1, NEMA 12

Handle Length

4 in

Mounting

Right

Type

Switch and operating mechanism with handle

Wire size

#14-1/0 AWG Cu/Al

Performance Ratings

Amperage Rating

100A

Depth range

7-16 in

Fuse clip rating

100 A at 250/600 V

HP rating - max

25 hp at 208 Vac, 30 hp at 240 Vac, 60 hp at 480 Vac, 75 hp at 600 Vac, 20 hp at 250 Vdc

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - C361SE1263](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)