

Eaton C65DND330AC

Catalog Number: C65DND330AC

Eaton definite purpose contactor, 30A, 110-120 Vac, 50/60 Hz, 1NO, 1NC, Open with metal mounting plate, 15-50A, two and three pole, 30A, Contactor, Three-pole, 40A, Screw/pressure plate and quick connect terminals (side-by-side), Reversing

General specifications



Photo is representative

| | |
|----------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C65DND330AC |
| UPC | Product Length/Depth |
| 782116417698 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 5 in |
| Product Weight | Warranty |
| 2.6 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified |

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Reversing

Coil

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contacto

Resistive load

40 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DND330AC](#)