

Eaton C65DNJ350B

Catalog Number: C65DNJ350B

Eaton definite purpose contactor, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 50A, Contactor, 3 Pole, 65A, Box lugs (posidrive setscrew) and quick connect terminals (vertical-in-line), Reversing

General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C65DNJ350B
UPC	Product Length/Depth
782116366217	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified



defaultTaxonomyAttributeLabel

Amperage Rating

50A

Number Of Poles

Three-pole

Type

Reversing

Coil

208-240 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

50 A

Model

Contactors

Resistive load

65 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals
(vertical-in-line)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C65DNJ3 2D PDF](#)

[C65DNJ3 3D Inventor](#)

[C65DNJ3 2D Drawing Xchange](#)

[C65DNJ3 AutoCAD 2D Footprint](#)

[C65DNJ3 AutoCAD 2D Footprint \(mm\)](#)

[C65DNJ3 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DNJ350B](#)