

Eaton C65DRC2301T

Catalog Number: C65DRC2301T

Eaton definite purpose contactor, Quick, 30A, 24 Vdc, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, 30A, Contactor, Two-pole, 40A, Screw/pressure plate, Reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C65DRC2301T
UPC	Product Length/Depth
782116483020	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Two-pole

Type

Reversing

Coil

24 Vdc

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactors

Resistive load

40 A

Terminals

Screw/pressure plate

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRC2301T](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)