

Eaton C65DRC3151T

Catalog Number: C65DRC3151T

Eaton definite purpose contactor, Quick, 15A, 24 Vdc, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, 15A, Contactor, Three-pole, 20A, Screw/pressure plate, Reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C65DRC3151T
UPC	Product Length/Depth
782116483501	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized
	CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

15A

Number Of Poles

Three-pole

Type

Reversing

Coil

24 Vdc

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

15 A

Model

Contactora

Resistive load

20 A

Terminals

Screw/pressure plate

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRC3151T](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)