

# Eaton C65DRC315B

Catalog Number: C65DRC315B

Eaton definite purpose contactor, Reversing contactors, 15–50A, two- and three-pole, Open with DIN rail mounting adapter, Screw/pressure plate, Three Pole, 15A, 208–240 Vac, 50/60 Hz

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C65DRC315B
<b>UPC</b>	<b>Product Length/Depth</b>
782116483525	3.35 in
<b>Product Height</b>	<b>Product Width</b>
3.75 in	5 in
<b>Product Weight</b>	<b>Warranty</b>
2.6 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	CSA Certified
	UL Recognized

## defaultTaxonomyAttributeLabel

### Amperage Rating

15A

### Number Of Poles

Three-pole

### Type

Reversing

### Coil

208-240 Vac, 50/60 Hz

### Enclosure

Open with DIN rail mounting adapter

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

15 A

### Model

Contactors

### Resistive load

20 A

### Terminals

Screw/pressure plate

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - C65DRC315B](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)