

Eaton C65DRC3301T

Catalog Number: C65DRC3301T

Eaton definite purpose contactor, Quick, 30A, 24 Vdc, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, 30A, Contactor, Three-pole, 40A, Screw/pressure plate, Reversing

General specifications



Photo is representative

Product Name

Eaton definite purpose contactor

Catalog Number

C65DRC3301T

UPC

782116483822

Product Length/Depth

3.35 in

Product Height

3.75 in

Product Width

5 in

Product Weight

2.6 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

CSA Certified
UL Recognized



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Reversing

Coil

24 Vdc

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contacto

Resistive load

40 A

Terminals

Screw/pressure plate

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRC3301T](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)