

Eaton C65DRC330A

Catalog Number: C65DRC330A

Eaton definite purpose contactor, Quick, 30A, 110-120 Vac, 50/60 Hz, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, 30A, Contactor, Three-pole, 40A, Screw/pressure plate, Reversing

General specifications



Photo is representative

| | |
|----------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C65DRC330A |
| UPC | Product Length/Depth |
| 782116483839 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 5 in |
| Product Weight | Warranty |
| 2.6 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified |

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactors

Resistive load

40 A

Terminals

Screw/pressure plate

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRC330A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)