

Eaton C65DRD225A

Catalog Number: C65DRD225A

Eaton definite purpose contactor, Quick, 25A, 110-120 Vac, 50/60 Hz, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, 25A, Contactor, Two-pole, 35A, Screw/pressure plate and quick connect terminals (side-by-side), Reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C65DRD225A
UPC	Product Length/Depth
782116482917	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

25A

Number Of Poles

Two-pole

Type

Reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

25 A

Model

Contactor

Resistive load

35 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C65DRD2 AutoCAD 2D Footprint \(mm\)](#)

[C65DRD2 2D PDF](#)

[C65DRD2 3D Inventor](#)

[C65DRD2 3D Model Xchange](#)

[C65DRD2 2D Drawing Xchange](#)

[C65DRD2 AutoCAD 2D Footprint](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRD225A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)