

Eaton C65DRE250A

Catalog Number: C65DRE250A

Eaton definite purpose contactor, Quick, 50A, 110-120 Vac, 50/60 Hz, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, 50A, Contactor, Two-pole, 65A, Box lugs (posidrive setscrew), Reversing

General specifications




Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C65DRE250A
UPC	Product Length/Depth
782116483358	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

50A

Number Of Poles

Two-pole

Type

Reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

50 A

Model

Contactors

Resistive load

65 A

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRE250A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)