

Eaton C65DRF240A

Catalog Number: C65DRF240A

Eaton definite purpose contactor, Quick, 40A, 110-120 Vac, 50/60 Hz, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, Two-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Reversing

Photo is representative

General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C65DRF240A
UPC	Product Length/Depth
782116483235	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified



defaultTaxonomyAttributeLabel

Amperage Rating

40A

Number Of Poles

Two-pole

Type

Reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactors

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C65DRF2 3D Model Xchange](#)

[C65DRF2 AutoCAD 2D Footprint \(mm\)](#)

[C65DRF2 AutoCAD 2D Footprint](#)

[C65DRF2 2D Drawing Xchange](#)

[C65DRF2 2D PDF](#)

[C65DRF2 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRF240A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia