

Eaton C65DRF340T

Catalog Number: C65DRF340T

Eaton definite purpose contactor, Quick, 40A, 24 Vac, 50/60 Hz, Open with DIN rail mounting adapter, 15-50A, two- and three-pole, Three-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C65DRF340T
UPC	Product Length/Depth
782116484058	3.35 in
Product Height	Product Width
3.75 in	5 in
Product Weight	Warranty
2.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

40A

Number Of Poles

Three-pole

Type

Reversing

Coil

24 Vac, 50/60 Hz

Enclosure

Open with DIN rail mounting adapter

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactor

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C65DRF3 2D Drawing Xchange](#)

[C65DRF3 AutoCAD 2D Footprint](#)

[C65DRF3 AutoCAD 2D Footprint \(mm\)](#)

[C65DRF3 2D PDF](#)

[C65DRF3 3D Model Xchange](#)

[C65DRF3 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - C65DRF340T](#)