

# Eaton C65FNF360A

Catalog Number: C65FNF360A

Eaton definite purpose contactor, Quick, 60A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 60A, Three-pole, 75A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Reversing

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton definite purpose contactor	C65FNF360A
<b>UPC</b>	<b>Product Length/Depth</b>
782113499345	10 in
<b>Product Height</b>	<b>Product Width</b>
4.5 in	6 in
<b>Product Weight</b>	<b>Warranty</b>
5 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL Recognized CSA Certified
<b>Catalog Notes</b>	
Resistive Load rating per pole	

## defaultTaxonomyAttributeLabel

### Amperage Rating

60A

### Number Of Poles

Three-pole

### Type

Reversing

### Coil

110-120 Vac, 50/60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

60 A

### Model

Contactors

### Resistive load

75 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C65FNF3 AutoCAD 2D Footprint \(mm\)](#)

[C65FNF3 3D Model Xchange](#)

[C65FNF3 3D Inventor](#)

[C65FNF3 2D PDF](#)

[C65FNF3 2D Drawing Xchange](#)

[C65FNF3 AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - C65FNF360A](#)