

Eaton CES2213

Catalog Number: CES2213

Eaton Crouse-Hinds series Arktite CES receptacle, 7A/30A, Through feed, 2-wire, 3-pole, Brass or copper contacts, Style 2, 0.5 HP/1.5 HP, Copper-free alum, Single-phase, Spring door, 3/4", Delay action circuit breaker, 120-240/480 Vac



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CES receptacle	CES2213
	UPC
	782274127507
Product Length/Depth	Product Height
4.13 in	7.44 in
Product Width	Product Weight
4.63 in	4.85 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Product specifications

Trade size

3/4"

Grounding style

Style 2

Configuration

Two-wire, three-pole

Phase

Single-phase

Horsepower

0.50 hp, 1.50 hp

Amperage Rating

7A/30A

Voltage rating

120-240 Vac/480 Vac

Receptacle style

Spring door

Back box style

Through feed

Material

Copper-free aluminum

Contact material

Hand-drawn copper

Brass

Type

Delayed action circuit breaking

Resources

Catalogs

[Arktite CES and CPH Explosionproof Receptacles and Plugs catalog page](#)

Certification reports

[Arktite CES and CPH Explosionproof Receptacles and Plugs Canadian certification](#)

[Arktite CES and CPH Explosionproof Receptacles and Plugs UL certification](#)

Specifications and datasheets

Eaton Specification Sheet - CES2213



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)