

# Eaton CES2214

Catalog Number: CES2214

Eaton Crouse-Hinds series Arktite CES receptacle, 7A/30A, Through feed, Three-wire, four-pole, Brass or copper contact, Style 2, 1 HP/3 HP, Copper-free aluminum, 3-phase, Spring door, 3/4", Delayed action circuit breaking, 120-240/480 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CES receptacle	CES2214
	UPC
	782274127606
Product Length/Depth	Product Height
4.13 in	7.44 in
Product Width	Product Weight
4.63 in	5.05 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

## Product specifications

### Trade size

3/4"

### Grounding style

Style 2

### Configuration

Three-wire, four-pole

### Phase

Three-phase

### Horsepower

1 hp/3 hp

### Amperage Rating

7A/30A

### Voltage rating

120-240 Vac/480 Vac

### Receptacle style

Spring door

### Back box style

Through feed

### Material

Copper-free aluminum

### Contact material

Brass

Hand-drawn copper

### Type

Delayed action circuit breaking

## Resources

### Catalogs

[Arktite CES and CPH Explosionproof Receptacles and Plugs catalog page](#)

### Certification reports

[Arktite CES and CPH Explosionproof Receptacles and Plugs UL certification](#)

[Arktite CES and CPH Explosionproof Receptacles and Plugs Canadian certification](#)

Specifications and datasheets

Eaton Specification Sheet - CES2214

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)