

Eaton CG50 250SA

Catalog Number: CG50 250SA

Eaton Crouse-Hinds series CG color-coded cord grip, Cable range min/max: 0.15-0.25", Red, Straight, Aluminum, 1/2"



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series CG color-coded cord grip	CG50 250SA
	UPC
	662277037273
Product Length/Depth	Product Height
1.31 in	1.07 in
Product Width	Product Weight
1.07 in	0.05 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Connector type

Straight

Material

Aluminum

Trade size

1/2"

Color

Red

Cable range (min/max)

0.15-0.25"

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CG50 250SA 3D drawing](#)

Catalogs

[Crouse-Hinds series CG Color-coded Cord Grips catalog page](#)

Certification reports

[CG Color-coded Cord Grips Canadian certification](#)

[CG Color-coded Cord Grips UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - CG50 250SA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)