

Eaton CGBS1013

Catalog Number: CGBS1013

Eaton Crouse-Hinds series CGBS portable cord connector, Non-armoured cable, Steel, Outer sheath min/max: 0.312-0.437", Explosionproof, 1/2" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGBS portable cord connector	CGBS1013
	UPC
	782274141114
Product Length/Depth	Product Height
5.25 in	0.44 in
Product Width	Product Weight
0.44 in	0.48 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Protection type

Explosion-proof

Cable type

Non-armoured

Gland type

Portable cord connector

Thread Size

1/2"

Thread type

NPT

Outer sheath (min/max)

0.312-0.437"

Material

Steel

Resources

Catalogs

[Crouse-Hinds series CGBS catalog page](#)

Installation instructions

[IF 1749 - CGBS Cord Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - CGBS1013](#)