

Eaton CGBS2014

Catalog Number: CGBS2014

Eaton Crouse-Hinds series CGBS portable cord connector, Non-armoured cable, Steel, Outer sheath min/max: 0.375-0.500", Explosionproof, 3/4" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGBS portable cord connector	CGBS2014
	UPC
	782274142500
Product Length/Depth	Product Height
5.25 in	0.75 in
Product Width	Product Weight
0.75 in	0.45 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Protection type

Explosion-proof

Cable type

Non-armoured

Gland type

Portable cord connector

Thread Size

3/4"

Thread type

NPT

Outer sheath (min/max)

0.375-0.500"

Material

Steel

Resources

Catalogs

[Crouse-Hinds series CGBS catalog page](#)

Installation instructions

[IF 1749 - CGBS Cord Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - CGBS2014](#)