

Eaton CGBS3015K

Catalog Number: CGBS3015K

Eaton Crouse-Hinds series CGBS portable cord connector, Non-armoured cable, Steel, Outer sheath min/max: 0.500-0.625", Explosionproof, Wire mesh grip, 1" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGBS portable cord connector	CGBS3015K
	UPC
	662276479265
Product Length/Depth	Product Height
2.88 in	0.63 in
Product Width	Product Weight
0.63 in	0.6 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Protection type

Explosion-proof

Cable type

Non-armoured

Gland type

Portable cord connector

Thread Size

1"

Thread type

NPT

Outer sheath (min/max)

0.500-0.625"

Material

Steel

Special features

Wire mesh grip

Resources

Catalogs

[Crouse-Hinds series CGBS catalog page](#)

Installation instructions

[IF 1749 - CGBS Cord Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - CGBS3015K](#)