

# Eaton CH224MTBP

Catalog Number: CH224MTBP

Eaton meter socket, Safety socket, 200A, Over, 4-jaw, 1-ph, With T-Fuse switch, 3-wire, 200 kA, Ring, 120/240 Vac



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton meter socket	CH224MTBP
<b>UPC</b>	<b>Product Length/Depth</b>
782116153718	50 in
<b>Product Height</b>	<b>Product Width</b>
7 in	16 in
<b>Product Weight</b>	<b>Warranty</b>
38 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	
UL Listed	

Type

Safety socket

Amperage Rating

200A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Secondary circuit breaker

200A

Number of wires

Three-wire

Security

Ring

Voltage rating

120/240V

Wire size

#6 AWG-250 kcmil

Accessories

With T-Fuse switch

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH224MTBP](#)