

Eaton CHM1G9N9NSU

Catalog Number: CHM1G9N9NSU

Eaton pedestal mount metered, Water and tamper resistant center/right receptacle, Metered-ring, Ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GF, NEMA 14-50R, NEMA 5-20R2GFI



Photo is representative

General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHM1G9N9NSU
UPC	Product Length/Depth
786685970790	31 in
Product Height	Product Width
7.5 in	10 in
Product Weight	Warranty
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL 231 UL Listed file E163588	0

Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Bottom

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 14-50R

Receptacle right

NEMA 5-20R2GFI

Type

Metered-ring

Miscellaneous

Special features

Water and tamper resistant center/right receptacle

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHM1G9N9NSU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia