

Eaton CHM1G9N9NSUPR

Catalog Number: CHM1G9N9NSUPR

Eaton pedestal mount metered, No prop rod, Metered-ring, Ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, Water and tamper resistant center and right receptacle, NEMA 5-20R2GF, NEMA 14-50R, NEMA 5-20R2GFI



Photo is representative

General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHM1G9N9NSUPR
UPC	Product Length/Depth
786685690025	8 in
Product Height	Product Width
31 in	10 in
Product Weight	Warranty
30 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed file E163588 UL 231	For receptacle configurations, see table in catalog.

Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle

Water and tamper resistant center and right receptacle

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 14-50R

Receptacle right

NEMA 5-20R2GFI

Type

Metered-ring

Miscellaneous

Special features

No prop rod

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHM1G9N9NSUPR

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia