

# Eaton CHM9N9NSU

Catalog Number: CHM9N9NSU

Eaton pedestal mount metered, Water and tamper resistant left/center receptacle, Metered-ring, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI WT TR, NEMA 5-20R2GFI WR TR



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount metered	CHM9N9NSU
<b>UPC</b>	<b>Product Length/Depth</b>
786685984957	30.8 in
<b>Product Height</b>	<b>Product Width</b>
7.1 in	9.7 in
<b>Product Weight</b>	<b>Warranty</b>
29.5 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL 231  
UL Listed file E163588

## defaultTaxonomyAttributeLabel

## Resources

### Special features

Water and tamper resistant left/center receptacle

### Type

Metered-ring

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

None

### Receptacle center

NEMA 5-20R2GFI WRTR

### Receptacle left

NEMA 5-20R2GFI WRTR

### Receptacle right

None

### Feed type

Bottom

### Mounting

Surface

### Number of circuits

4

### Specifications and datasheets

[Eaton Specification Sheet - CHM9N9NSU](#)