

# Eaton CN35DN2EB

Catalog Number: CN35DN2EB

Eaton CN35 electrically held lighting contactor, 30 A, 1 NO, 208 V/60 Hz, 30 A, Open type, Two-pole, Electrically held, CN35, Lighting contactors

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CN35 electrically held lighting contactor	CN35DN2EB
	UPC
	782113781037
<b>Product Length/Depth</b>	<b>Product Height</b>
3.49 in	3.88 in
<b>Product Width</b>	<b>Product Weight</b>
2 in	1.4 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed

Number Of Poles

Two-pole

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Quick Selector - Lighting Contactors](#)

[Eaton Specification Sheet - CN35DN2EB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)