

# Eaton CN35DN4HB

Catalog Number: CN35DN4HB

Eaton CN35 electrically held lighting contactor, 30 A, 1 NO, 30 A, Open type, Four-pole, Electrically held, CN35, Lighting contactors

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CN35 electrically held lighting contactor	CN35DN4HB
	<b>UPC</b>
	782113064680
<b>Product Length/Depth</b>	<b>Product Height</b>
3.52 in	4.35 in
<b>Product Width</b>	<b>Product Weight</b>
4.2 in	2.9 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed

Number Of Poles

Four-pole

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Eaton Specification Sheet - CN35DN4HB](#)

[Quick Selector - Lighting Contactors](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)