

# Eaton CN35GN2AB

Catalog Number: CN35GN2AB

Eaton CN35 electrically held lighting contactor- Open Type , 60 A, 1 NO , Two-pole, Electrically held, CN35, Lighting contactors

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CN35 electrically held lighting contactor	CN35GN2AB
	<b>UPC</b>
	782113982328
<b>Product Length/Depth</b>	<b>Product Height</b>
4.44 in	5.05 in
<b>Product Width</b>	<b>Product Weight</b>
2.56 in	3.5 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL Listed
	CSA Certified

defaultTaxonomyAttributeLabel

## Resources

### Type

Electrically held lighting contactor

### Brochures

[Lighting contactors](#)

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

### Specifications and datasheets

[Eaton Specification Sheet - CN35GN2AB](#)

[Quick Selector - Lighting Contactors](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)