

Eaton CN35GN3EB

Catalog Number: CN35GN3EB

Eaton CN35 Electrically held lighting contactor- Open Type , 60 A, 1 NO , Three-pole, Electrically held, CN35, Lighting contactors , 208 V/60 Hz coil

General specifications



Photo is representative

Product Name	Catalog Number
Eaton CN35 electrically held lighting contactor	CN35GN3EB
	UPC
	782113000671
Product Length/Depth	Product Height
4.44 in	5.05 in
Product Width	Product Weight
2.56 in	3.5 lb
Warranty	Certifications
1 year	CSA Certified
	UL Listed

Number Of Poles

Three-pole

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Eaton Specification Sheet - CN35GN3EB](#)

[Quick Selector - Lighting Contactors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia