

# Eaton CN35KN3H

Catalog Number: CN35KN3H

Eaton CN35 electrically held lighting contactor, 100 A, 1 NO, 277 V/60 Hz, 100 A, Three-pole, Electrically held, CN35 Series, Lighting contactors



Photo is representative

## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                             | <b>Catalog Number</b> |
| Eaton CN35 electrically held lighting contactor | CN35KN3H              |
|   | UPC                   |
|   | 782113644097          |
| <b>Product Length/Depth</b>                     | <b>Product Height</b> |
| 5.94 in   | 7.17 in               |
| <b>Product Width</b>                            | <b>Product Weight</b> |
| 3.54 in   | 9 lb                  |
| <b>Warranty</b>                                 | <b>Certifications</b> |
| 1 year  | UL Listed             |
|   | CSA Certified         |

Number Of Poles

Three-pole

Brochures

Lighting contactors

Catalogs

Eaton's Volume 5—Motor Control and Protection

Multimedia

S1. E4. Ask the Experts - NEMA, IEC and DP contactors

Specifications and datasheets

Quick Selector - Lighting Contactors

Eaton Specification Sheet - CN35KN3H



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia