

Eaton CPH7733

Catalog Number: CPH7733

Eaton Crouse-Hinds series Arktite CPH plug, 30A/60A, 0.500-0.875" cable diameter, 2-wire, 3-pole, Brass or hard-drawn copper contacts, Style 2, 3 HP, Copper-free alum, Single-phase, Mechanical cable grip and neoprene bush, 120-240/480 Vac

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPH plug	CPH7733
	UPC
	782274173405
Product Length/Depth	Product Height
7.75 in	2.75 in
Product Width	Product Weight
2.75 in	1.85 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Product specifications

Grounding style

Style 2

Configuration

Two-wire, three-pole

Phase

Single-phase

Horsepower

3 hp

Amperage Rating

30A/60A

Voltage rating

120-240 Vac/480 Vac

Cable diameter

0.500-0.875 in

Material

Copper-free aluminum

Contact material

Brass

Hand-drawn copper

Special features

Mechanical cable grip and neoprene bushing

Resources

Catalogs

[Arktite CES and CPH Explosionproof Receptacles and Plugs catalog page](#)

Certification reports

[Arktite CES and CPH Explosionproof Receptacles and Plugs UL certification](#)

[Arktite CES and CPH Explosionproof Receptacles and Plugs Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - CPH7733](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)