

Eaton CPP4553

Catalog Number: CPP4553

Eaton Crouse-Hinds series Arktite CPP plug, 7A/30A, 0.375-0.875" cable diameter, Two-wire, three-pole, Brass contacts, 60 Hz, Style 2, 0.5 HP/1.5 HP, Copper-free alum, Factory sealed, Delayed action circuit breaking, 125-250 Vac/480 Vac

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPP plug	CPP4553
	UPC
	782274175805
Product Length/Depth	Product Height
6.38 in	2.5 in
Product Width	Product Weight
2.5 in	1.175 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Product specifications

Grounding style

Style 2

Amperage Rating

7A/30A

Configuration

Two-wire, three-pole

Cable diameter

0.375-0.875 in

Voltage rating

125-250 Vac/480 Vac

Horsepower

0.50 hp, 1.50 hp

Frequency rating

60 Hz

Material

Copper-free aluminum

Contact material

Brass

Special features

Factory sealed

Type

Delayed action circuit breaking

Resources

Catalogs

[Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page](#)

Certification reports

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification](#)

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification](#)

Installation instructions

[IF 285 - CPP Plugs](#)

Specifications and datasheets

Eaton Specification Sheet - CPP4553



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)