

Eaton CPP516

Catalog Number: CPP516

Eaton Crouse-Hinds series Arktite CPP plug, 20A, 0.312-0.625" cable diameter, Two-wire, three-pole, Brass contacts, 60 Hz, Style 2, 1 HP, Copper-free aluminum, Factory sealed, Delayed action circuit breaking, 125-250 Vac/18 Vdc

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPP plug	CPP516
	UPC
	782274175102
Product Length/Depth	Product Height
8.38 in	1.75 in
Product Width	Product Weight
1.75 in	0.8 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Product specifications

Grounding style

Style 2

Amperage Rating

20A

Configuration

Two-wire, three-pole

Cable diameter

0.312-0.625 in

Voltage rating

125-250 Vac/18 Vdc

Horsepower

1 hp

Frequency rating

60 Hz

Material

Copper-free aluminum

Contact material

Brass

Special features

Factory sealed

Type

Delayed action circuit breaking

Resources

Catalogs

[Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page](#)

Certification reports

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification](#)

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification](#)

Installation instructions

[IF 285 - CPP Plugs](#)

Specifications and datasheets

Eaton Specification Sheet - CPP516



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia