

Eaton CPR154

Catalog Number: CPR154

Eaton Crouse-Hinds series Arktite CPR connector, 20A, 0.375-0.625" cable diameter, 2-wire, 3-pole, Brass contacts, 60 Hz, Style 2, 1 HP, Copper-free alum, Spring door, Factory sealed, Delayed action circuit breaking, 125-250 Vac/18 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPR connector	CPR154
	UPC
	782274177700
Product Length/Depth	Product Height
7.56 in	5 in
Product Width	Product Weight
3 in	1.95 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Product specifications

Grounding style

Style 2

Amperage Rating

20A

Configuration

Two-wire, three-pole

Cable diameter

0.375-0.625 in

Receptacle style

Spring door

Voltage rating

125-250 Vac/18 Vdc

Horsepower

1 hp

Frequency rating

60 Hz

Material

Copper-free aluminum

Contact material

Brass

Special features

Factory sealed

Type

Delayed action circuit breaking

Resources

Catalogs

[Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page](#)

Certification reports

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification](#)

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification](#)

Installation instructions

IF 1080 - CPR Cable Connector Receptacles

Specifications and datasheets

Eaton Specification Sheet - CPR154



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)