

# Eaton CPS532R

Catalog Number: CPS532R

Eaton Crouse-Hinds series Arktite CPS receptacle, 7A/30A, Two-wire, three-pole, Brass contacts, 60 Hz, Style 2, 0.5 HP/1.5 HP, Copper-free aluminum, Factory sealed, Delayed action circuit breaking, 125-250 Vac/480 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPS receptacle	CPS532R
	UPC
	782274184906
Product Length/Depth	Product Height
5.125 in	6.72 in
Product Width	Product Weight
3.5 in	2.2 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

## Product specifications

### Grounding style

Style 2

### Amperage Rating

7A/30A

### Configuration

Two-wire, three-pole

### Voltage rating

125-250 Vac/480 Vac

### Horsepower

0.50 hp, 1.50 hp

### Frequency rating

60 Hz

### Material

Copper-free aluminum

### Contact material

Brass

### Special features

Factory sealed

### Type

Delayed action circuit breaking

## Resources

### Catalogs

[Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page](#)

### Certification reports

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification](#)

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification](#)

### Installation instructions

[IF 165 - CPS Receptacles](#)

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

### Specifications and datasheets



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)