

Eaton CPS532 201

Catalog Number: CPS532 201

Eaton Crouse-Hinds series Arktite CPS receptacle assembly, 7A/30A, Dead end, 2-wire, 3-pole, Brass contacts, 60 Hz, Style 2, 0.5 HP/1.5 HP, Copper-free alum, Single-gang, Fact seal, 3/4", Delay action circuit brk, 125-250 Vac/480 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPS receptacle assembly	CPS532 201
	UPC
	782274184104
Product Length/Depth	Product Height
3.5 in	6.72 in
Product Width	Product Weight
7.25 in	6.95 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Product specifications

Grounding style

Style 2

Number of gangs

Single-gang

Amperage Rating

7A/30A

Configuration

Two-wire, three-pole

Back box style

Dead end

Trade size

3/4"

Voltage rating

125-250 Vac/480 Vac

Horsepower

0.50 hp, 1.50 hp

Frequency rating

60 Hz

Material

Copper-free aluminum

Contact material

Brass

Special features

Factory sealed

Type

Delayed action circuit breaking

Resources

Catalogs

Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page

Certification reports

Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors
UL certification

Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors

Canadian certification

Installation instructions

IF 165 - CPS Receptacles

IF 1424 - DSD, GFS, CPS and ENR Replacement Covers

Specifications and datasheets

Eaton Specification Sheet - CPS532 201



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)