

# Eaton CPS532 312

Catalog Number: CPS532 312

Eaton Crouse-Hinds series Arktite CPS receptacle assembly, 7A/30A, Through feed, 2-wire, 3-pole, Brass contacts, 60 Hz, Style 2, 0.5 HP/1.5 HP, Copper-free alum, 2-gang, Fact seal, 1", Delay action circuit brk, 125-250 Vac/480 Vac

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPS receptacle assembly	CPS532 312
	UPC
	782274184807
Product Length/Depth	Product Height
7.19 in	6.72 in
Product Width	Product Weight
7.25 in	14.28 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

## Product specifications

### Grounding style

Style 2

### Number of gangs

Two-gang

### Amperage Rating

7A/30A

### Configuration

Two-wire, three-pole

### Back box style

Through feed

### Trade size

1"

### Voltage rating

125-250 Vac/480 Vac

### Horsepower

0.50 hp, 1.50 hp

### Frequency rating

60 Hz

### Material

Copper-free aluminum

### Contact material

Brass

### Special features

Factory sealed

### Type

Delayed action circuit breaking

## Resources

### Catalogs

Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page

### Certification reports

Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors  
UL certification

Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors

Canadian certification

### Installation instructions

IF 165 - CPS Receptacles

IF 1424 - DSD, GFS, CPS and ENR Replacement Covers

### Specifications and datasheets

Eaton Specification Sheet - CPS532 312



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)