

Eaton CWL515P-BU

Catalog Number: CWL515P-BU

Eaton safety grip locking plug, Bulk pack, #16-12 AWG, 15A, Industrial, 125V, Back wiring, Black, white, Safety grip, L5-15, Two-pole, Three-wire, Nylon, 0.38 to 1 in, -40° to 60°C



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart safety grip locking plug	CWL515P-BU
UPC	Product Length/Depth
032664702600	4.25 in
Product Height	Product Width
1.75 in	2 in
Product Weight	Compliances
0.15 lb	RoHS Compliant
Certifications	
Federal Specification Classification W-C-596F	
cULus Listed	
CSA certified	

defaultTaxonomyAttributeLabel

Special features

Bulk pack

Type

Locking plug

Amperage Rating

15A

Voltage rating

125 V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back

Number of wires

3

Grounding

Number Of Poles

Two-pole

Color

Black

White

Cord diameter

0.33-0.66 in (8.4-16.7 mm)

Material

Nylon

Operating temperature

-40 to 60 °C (-40 to 140 °F)

Allowable wire size

#16-12 AWG

NEMA configuration

L5-15

Torque rating

14 lbf-inch

Resources

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Industrial grade L5-15 locking devices spec sheet

Eaton Specification Sheet - CWL515P-BU

Design type

Safety grip

Face/body material

Nylon



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia