

Eaton D04010

Catalog Number: D04010

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 230 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 460Y/266V, 150°C, 14 kVA, Al windings, Frame: 912B, uses WS38



Photo is representative

General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Drive isolation ventilated transformer | D04010 |
| | UPC |
| | 786680330421 |
| Product Length/Depth | Product Height |
| 16.5 in | 30 in |
| Product Width | Product Weight |
| 23 in | 158 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

912B

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Horsepower

10 hp

Kva Rating

14 kVA

Phase

Three-phase

Primary voltage

230 V

Secondary Voltage

460Y/266 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - D04010](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)