

# Eaton D04401

Catalog Number: D04401

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 230 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 575Y/332V, 150°C, 14 kVA, Al windings, Frame: 912B, uses WS38



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Drive isolation ventilated transformer	D04401
	<b>UPC</b>
	786680330827
<b>Product Length/Depth</b>	<b>Product Height</b>
16.5 in	30 in
<b>Product Width</b>	<b>Product Weight</b>
23 in	198 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

DT-3

### Frame

912B

### Tap size

1 at +5% FCAN, 1 at -5% FCBN

### Type

Dry Type Distribution, Drive Isolation Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Horsepower

10 hp

### Kva Rating

14 kVA

### Phase

Three-phase

### Primary voltage

230 V

### Secondary Voltage

575Y/332 V

### Temperature rise

150 °C rise

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - D04401](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)